

7931A Multi-Conductor - Category 6 DataTwist® Twisted Pair Cable



For more Information
please call

1-800-Belden1



General Description:

23 AWG Bonded-Pairs solid bare copper conductors, FEP insulation, sunlight- oil- and gas-resistant FEP jacket. Sequential marking at two foot intervals.

Usage (Overall)

Suitable Applications: Industrial Ethernet Cable, Harsh Environments, 350MHz Enhanced Category 6, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, RJ-45 Compatible, High and Low Temperature, Oil and Gasoline Exposure, Limited Combustible FHC 25/50

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Cabling Fillers: Rod Center Member

Overall Nominal Diameter: 0.214 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Installation Temperature Range: -55°C To +150°C

Operating Temperature Range: -70°C To +150°C

Bulk Cable Weight: 28 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

Min. Bend Radius/Minor Axis: 0.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP, FHC 25/50, UL444

NEC Articles: NFPA 259

CEC/C(UL) Specification: CMP

7931A Multi-Conductor - Category 6 DataTwist® Twisted Pair Cable

EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	UL verified to Category 6

Applicable Patents:

Country
www.belden.com/p

Flame Test

CSA Flame Test:	FT6
-----------------	-----

Suitability

Oil Resistance:	Yes
-----------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)
15

Maximum Capacitance Unbalance (pF/100 m):	330
---	-----

Nominal Velocity of Propagation:

VP (%)
72

Maximum Delay:

Delay (ns/100 m)
537 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9.38

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
5

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	74.3	72.3	72.3	70.3	20.0	na
4	3.8	65.3	63.3	61.5	59.5	23.0	na
8	5.3	60.8	58.8	55.4	53.4	24.5	na
10	6.0	59.3	57.3	53.3	51.3	25.0	na
16	7.6	56.2	54.3	48.7	46.7	25.0	na
20	8.5	54.8	52.8	46.3	44.3	25.0	na
25	9.5	53.3	51.3	43.8	41.8	24.3	na
31.25	10.7	51.9	49.9	41.2	39.2	23.6	na
62.5	15.4	47.4	45.4	32.0	30.0	21.5	na
100	19.8	44.3	42.3	24.5	22.5	20.1	na
155	25.2	41.5	39.5	16.3	14.3	18.8	na
200	29.0	39.8	37.8	10.8	8.8	18.0	na
250	32.8	38.3	36.3	5.5	3.5	17.3	na

Premise Cable Electrical Table 2:

7931A Multi-Conductor - Category 6 DataTwist® Twisted Pair Cable

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	67.8	64.8
4	100 ± 15	100 ± 15	55.8	52.7
8	100 ± 15	100 ± 15	49.7	46.7
10	100 ± 15	100 ± 15	47.8	44.8
16	100 ± 15	100 ± 15	43.7	40.7
20	100 ± 15	100 ± 15	41.8	38.7
25	100 ± 15	100 ± 15	39.8	36.8
31.25	100 ± 15	100 ± 15	37.9	34.9
62.5	100 ± 15	100 ± 15	31.9	28.8
100	100 ± 15	100 ± 15	27.8	24.8
155	100 ± 22	100 ± 15	23.9	20.9
200	100 ± 22	100 ± 15	21.8	18.7
250	100 ± 32	100 ± 15	19.8	16.8

Notes (Overall)

Notes: Operating temperatures subject to length de-rating.

Notes (Cont'd.):

Cable passes -70C Cold Bend per UL 1581. T568A Plug Compatible Part Number: R301603 T568B Plug Compatible Part Number: R301604

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7931A 0101000	1,000 FT	37.000 LB	BLACK		4 PR #23 FEP FEP

Revision Number: 7 Revision Date: 07-19-2016

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.