



PAR30/PAR20 LED

12.5PAR30L/F25 4000 DIM SO

Philips PAR30 and PAR20 LED Single Optic Lamps provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	12.7-75W

Light Technical	
Color Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	950 lm
Luminous Flux (Rated) (Nom)	950 lm
Luminous Intensity (Nom)	5200 cd
Color Designation	Cool White (CW)
Rated Beam Angle	25 °
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	12.7 W

Lamp Current (Nom)	125 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Max)	0.5 s
Power Factor (Nom)	0.85
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	89 °C

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	Not applicable

Product Data	
Order product name	120V PAR30L 12.7W 25D 4000K 900 D SO
EAN/UPC - Product	046677454685
Order code	454686
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001132504

PAR30/PAR20 LED

Net Weight (Piece)	0.001 kg
--------------------	----------

Dimensional drawing



PAR30L CL 120V 12.5W-75W 25D 4000K E26 D

Product	D	C
120V PAR30L 12.7W 25D 4000K 900 D SO	92 mm	116 mm

PAR30/PAR20 LED

Photometric data

Accent Lighting - Spots

