



PAR30/PAR20 LED

12.5PAR30L/F35 3000 DIM SO

Philips PAR30 and PAR20 LED Single Optic Lamps provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data

General Information		Wattage Equivalent	
Cap-Base	E26 [Single Contact Medium Screw]		75 W
Nominal Lifetime (Nom)	25000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time To 60% Light (Nom)	0.5 s
Technical Type	12.7-75W	Power Factor (Nom)	0.85
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	89 °C
Beam Angle (Nom)	35 °		
Initial lumen (Nom)	900 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	900 lm	Dimmable	Yes
Luminous Intensity (Nom)	2400 cd		
Color Designation	White (WH)	Approval and Application	
Rated Beam Angle	35 °	Energy star mark	Energy star
Correlated Color Temperature (Nom)	3000 K	Suitable For Accent Lighting	Yes
Luminous Efficacy (rated) (Nom)	71 lm/W	Energy Efficiency Label (EEL)	Not applicable
Color Consistency	<6		
Color Rendering Index (Nom)	80	Product Data	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order product name	120V PAR30L 12.7W 35D 3000K 900 D SO
		EAN/UPC - Product	046677454708
		Order code	454702
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	6
		Material Nr. (12NC)	929001132704
Operating and Electrical			
Input Frequency	60 Hz		
Power (Rated) (Nom)	12.7 W		
Lamp Current (Nom)	125 mA		


PAR30/PAR20 LED

Net Weight (Piece)	0.001 kg
--------------------	----------

Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.
- CAUTION: Risk of electric shock— do not use where directly exposed to water
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005.



Dimensional drawing



PAR30L CL 120V 12.5W-75W 35D 3000K E26 D

Product	D	C
120V PAR30L 12.7W 35D 3000K 900 D SO	92 mm	116 mm

Photometric data



PAR30/PAR20 LED

