



GE
Lighting

10098 - GE Cool White Starcoat® T8

F13T8/CW

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	18 mg
Mercury-Picogram per mean lm hr	5000
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	480 lm
Nominal Initial Lumen per Watt	43
Initial Lumens-nominal	565 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10098
Description	F13T8/CW
Alternative Unit Of Measure	EACH
Standard Package Quantity	24
Ean UPC	043168100984
Standard Package GTIN	00043168100984
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
Sales Unit	Each
UCC	043168100984
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168100984
Standard Package GTIN	10043168100981
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168100984

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
Face to End of Opposing Pin (B) <Max>	11.5 in
Face to End of Opposing Pin (B) <Min>	11.4 in
Nominal Length	12.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	13 W

CAUTIONS & WARNINGS



Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection

installation or removal.



Jan 6, 2017 11:07:43 AM For additional information, visit www.gelighting.com