

# Technical Data Sheet

## Fire Alarm Cables

# WEST PENN WIRE



2833 West Chestnut Street  
Washington, PA 15301  
Toll Free: (800) 245-4964  
Fax: (724) 222-6420  
www.westpenn-wpw.com

---

<b>PART NUMBER:</b>	<b>994</b>
<b>DESCRIPTION:</b>	14/2 Solid bare copper conductors, unshielded with an overall jacket.
<b>NEC RATING:</b>	FPLR, NEC Article 760
<b>APPROVALS:</b>	(UL) Listed
<b>APPLICATION:</b>	Indoor for (Audio Circuits, Control Circuits, Initiating Circuits, Notification Circuits)

---

### Construction Parameters:

Conductor	14 AWG Bare Copper
Stranding	Solid
Insulation Material	Polypropylene
Insulation Thickness	0.010" Nom.
Number of Conductors	2
Shield	None
Drain	None
Jacket Material	PVC
Jacket Thickness	0.017" Nom.
Overall Cable Diameter	0.210" Nom.
Approximate Cable Weight	41 Lbs/1M' Nom.
Flame Rating	UL 1666 Riser Flame Test

---

### Electrical & Environmental Properties:

Temperature Rating	-20deg C to 60deg C
Operating Voltage	300 V RMS
Max.Capacitance Between Conductors @ 1 KHz	22 pf/ft Nom.
DC Resistance per Conductor @ 20deg C	2.5 Ohms/1M' Nom.
Nom. Impedance @ 1 KHz	91 Ohms
Insulation Colors	Black, Red
Jacket Color	Red, Blue, White, Yellow, Black
RoHS Compliant	Yes

---

### Mechanical Properties:

Max. Recommended Pull Tension	99.4 lbs.
Min. Bend Radius (Install)	2"



Specification Issue Date: 8/13

This document is the property of West Penn Wire.  
The information contained herein is considered  
Proprietary and not to be reproduced by any means  
Without written consent of West Penn Wire

Standard Lengths are 1000ft.  
The Jacket is sequentially footmarked.  
The information presented here is, to the best of our  
knowledge, is true and accurate. However, since  
conditions of use are beyond our control, all  
recommendations or suggestions are presented  
without guarantee or responsibility on our part. We  
disclaim all liability in connection with the use of  
information contained herein or otherwise.