




RIGID-IMC FITTINGS

Malleable Iron Threaded Conduit Bodies

[Download
Specification Sheet
\(\[https://www.sepco-usa.com/wp-content/uploads/2017/03/page_033.pdf\]\(https://www.sepco-usa.com/wp-content/uploads/2017/03/page_033.pdf\)\)](#)



[Print](#)



C1

Trade Size	1/2"
Dim A	5.375
Dim B	1.313
Dim C	1.375
MAX WIRE SIZE	N/A
VOL. CU.IN.	4.50
Unit Pack	10
Master Pack	50
Lbs. / 100 Pcs.	98
UPC	43010 50-M, C-61, C50M,
Competitor Part Number	C50M, LCM- 50, C-50, C17, C17,

APPLICATION FEATURES

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

Tapered threaded hubs (NPT)

Flat back design for easy mounting close to walls

Suitable for use in concrete

STANDARD MATERIALS STANDARD FINISH

Malleable Iron Zinc Plated

UL LISTED OPTIONAL FINISH

E198259



For additional corrosion protection, specify Hot Dipped Galvanized. Add suffix 'G' to Malleable Iron catalog number. Example LB1G. For

more
information,
see page 11.
