

SPECIFICATIONS

480 V Primary, 240/120 V Secondary



| | |
|------------------------------------|--|
| Transformer Type: | Isolation |
| Phase: | Three |
| Frequency: | 60 Hz |
| kVA: | 15 to 750 kVA |
| K Rating: | 1 |
| Primary Configuration: | Delta |
| Secondary Configuration: | Delta with Center Tap |
| Reverse Connectable: | Yes |
| Winding Material: | Aluminum |
| Electrostatically Shielded: | No |
| Temperature Rise: | 150°C |
| Insulation System: | 220°C |
| Enclosure Rating: | NEMA 1 |
| Enclosure Material: | Steel |
| Construction Style: | Enclosed - Ventilated Core & Coil |
| Mounting Type: | Floor |
| Connection Type: | Lugs/Bolt-down Terminals |
| Cooling: | Air/dry |
| Agency Approvals: | UL and CUL Listed, CSA Approved < 45 dB (10 to 50 kVA) < 50 dB (51 to 150 kVA) < 55 dB (151 to 300 kVA) < 60 dB (500 kVA) < 64 dB (750 kVA) |

Warranty: 1 Year

DIMENSIONS

All dimensions in inches.

| kVA | Weight (lbs) | Length | Width | Height | Wiring Diagram |
|------------|-------------------------|---------------|--------------|---------------|---------------------------|
| 15 | 210 | 19.38 | 17.13 | 29 | 21 |
| 30 | 370 | 19.88 | 22.38 | 34 | 21 |
| 45 | 400 | 19.88 | 22.38 | 34 | 21 |
| 75 | 575 | 19.88 | 26 | 37 | 21 |
| 112.5 | 760 | 23.5 | 28.5 | 43 | 21 |
| 150 | 1180 | 28 | 39 | 44.5 | 21A |
| 225 | 1520 | 30.5 | 42.13 | 51 | 21A |
| 300 | 1630 | 30.88 | 46.5 | 63 | 21A |
| 500 | 2335 | 36.88 | 53.38 | 72.75 | 21A |
| 750 | 3280 | 44.38 | 53.8 | 76.75 | 21A |

WIRING DIAGRAM

480 V Primary - 240/120 V Secondary

