



Reflector Flood

65BR30/FL 130V 12/1 PRO

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Bulb Shape	BR30 [BR30 (BR30)]
Operating Position	Universal [Universal]
Main Application	Indoor Reflector
Gas Filling	GAS
Life With 3 Hour Per Day Use	1.8 a

Light Technical	
Beam Angle (Nom)	300 °
Initial lumen (Nom)	605 lm
Beam Description	Flood [Flood]
Luminous Flux Lamp @ 120V	450 lm
Correlated Color Temperature (Nom)	2680 K

Operating and Electrical	
Power (Rated) (Nom)	65 W
Lamp Wattage Rated@120V	55 W
Voltage (Nom)	130 V

Mechanical and Housing	
Bulb Finish	Frosted (FR)
Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]

Approval and Application	
Estimated Energy Cost Per Year At 120V	6.67 \$
Estimated Energy Cost Per Year	7.83 \$

Product Data	
Order product name	65BR30/FL 130V 12/1 PRO
EAN/UPC - Product	046677140076
Order code	140079
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925190336106
Net Weight (Piece)	0.001 kg

Reflector Flood

Dimensional drawing

Product

65W E26 130V BR30 FR

