


LTR	REVISION	DATE	APPD
A	041516-GP01: ADDED MISSING DATA	04-27-16	GP



NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. SLEEVE MATERIAL: GENERAL POLYMERS RYNITE FR530 (UL 94HB)
3. BASE MATERIAL: BRASS, NICKEL-PLATED
4. OPERATING TEMPERATURE: ~-30°C TO ~+50°C

**FULL BEAM WIDTH @ 50% INTENSITY



ELECTRICAL - OPTICAL CHARACTERISTICS (Ta = 25°C)

REVISION NOTIFICATION	
<input type="checkbox"/>	DLC
<input type="checkbox"/>	UL/ETL
<input type="checkbox"/>	MADE IN USA
<input type="checkbox"/>	CUSTOMER _____
<input type="checkbox"/>	OTHER

BF321-0AG-120A	AQUA GREEN	120VAC	0.5 W	0.0047-0.0054 A	0.275cd	520	-	85°	AC Voltage
BF321-0CW-120A	COOL WHITE	120VAC	0.5 W	0.0047-0.0054 A	0.550cd	-	8000K	95°	AC Voltage
BF321-0IW-120A	WARM WHITE	120VAC	0.5 W	0.0047-0.0054 A	0.086cd	-	3000K	110°	AC Voltage
BF321-0ER-120A	SUPER RED	120VAC	-	0.0047-0.0054 A	-	630	-	90°	AC Voltage
BF321-0PB-120A	SUPER BLUE	120VAC	0.5 W	0.0047-0.0054 A	0.074cd	465	-	85°	AC Voltage
BF321-0UG-120A	SUPER GREEN	120VAC	0.5 W	0.0047-0.0054 A	0.029cd	573	-	90°	AC Voltage
BF321-0UO-120A	SUPER ORANGE	120VAC	0.5 W	0.0047-0.0054 A	0.065cd	610	-	90°	AC Voltage
BF321-0UR-120A	ULTRA RED	120VAC	0.5 W	0.0047-0.0054 A	0.050cd	652	-	80°	AC Voltage
BF321-0UY-120A	SUPER YELLOW	120VAC	0.5 W	0.0047-0.0054 A	0.039cd	593	-	85°	AC Voltage

LEDTRONICS PART NO.	COLOR EMITTED	INPUT VOLTAGE, V	POWER (W)	CURRENT (A)	MAXIMUM CANDELA	λ P nm	COLOR TEMP. (Kelvin)	VIEWING ANGLE**	CENTER CONTACT POLARITY
---------------------	---------------	------------------	-----------	-------------	-----------------	--------	----------------------	-----------------	-------------------------

<p>LEDTRONICS, INC. 23105 KASHIWA COURT TORRANCE, CA 90505</p>	<p>-PROPRIETARY- This document contains Proprietary information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.</p>	<p>TITLE BF321-0XX-120A</p>			
	<p>.XXX ± .010 TOLERANCE PER ANSI-Y14.5 .XX ± .025 (UNLESS OTHERWISE STATED) ANGLES ± 0°,30' FRACT. ± 1/32</p>	<p>DWG NO BF321-120VAC</p>	<p>SCALE 1:1</p>	<p>SHEET 1 OF 1</p>	<p>DATE 10-19-11</p>
	<p>CODE IDENT NO. 8Z410</p>	<p>DWG BY GP 10-19-11</p>	<p>CHK BY</p>	<p>QA EE 06-06-16</p>	<p>MFG LD 06-06-16</p>